

MGL1408 Seismic Configuration by sequence acquired with offsets

DR Table#	Seq #	line name	shot spacing (m)	streamer length (m)	sample rate (ms)	record length (sec)	source	source	streamer depth	NRP-COS	COS-CNG	number of channels	
							sub-array used	depth (m)					volume cu in
	001	MGL1408OBS001	225	8000	2	18	ALL	9	6600	9	216	307.5	636 channels
	002	MGL1408MCS002	50	8000	2	18	ALL	9	6600	9	216	307.5	636 channels
	003	MGL1408OBS003	225	8000	2	18	ALL	9	6600	9	216	307.5	636 channels
	004	MGL1408MCS003	50	8000	2	18	ALL	9	6600	9	216	307.5	636 channels
	005	MGL1408MCS031	50	8000	2	18	2 & 3	6	3300	6	216	307.5	636 channels
	006	MGL1408MCS032	50	8000	2	18	2 & 3	6	3300	6	216	307.5	636 channels
	007	MGL1408MCS033	25	6000	1	9	2 & 3	6	3300	6	216	307.5	480 channels
	008	MGL1408MCS034	25	6000	1	9	2 & 3	6	3300	6	216	307.5	480 channels
	009	MGL1408MCS035	37.5	6000	1	9	2 & 3	6	3300	6	216	307.5	480 channels
	010	MGL1408OBS04A	225	8000	2	18	ALL	9	6600	9	216	307.5	636 channels
	011	MGL1408MCS041	50	8000	2	18	2 & 3	6	3300	6	216	307.5	636 channels
	012	MGL1408MCS042	50	8000	2	18	2 & 3	6	3300	6	216	307.5	636 channels
	013	MGL1408OBS04B	225	8000	2	18	ALL	9	6600	9	216	307.5	636 channels
	014	MGL1408OBS01A	225	8000	2	18	ALL	9	6600	9	216	307.5	636 channels
	015	MGL1408OBS01B	225	8000	2	18	ALL	9	6600	9	216	307.5	636 channels
	016	MGL1408MCS01	50	8000	2	18	ALL	9	6600	9	216	307.5	636 channels
	017	MGL1408MCS01A	50	8000	2	18	ALL	9	6600	9	216	307.5	636 channels
	018	MGL1408MCS01B	50	8000	2	18	ALL	9	6600	9	216	307.5	636 channels
	019	MGL1408MCS052	25	6000	1	9	2 & 3	6	3300	6	216	307.5	480 channels
	020	MGL1408MCS053	25	6000	1	9	2 & 3	6	3300	6	216	307.5	480 channels
	021	MGL1408MCS057	25	6000	1	9	2 & 3	6	3300	6	216	307.5	480 channels
	022	MGL1408MCS058	25	6000	1	9	2 & 3	6	3300	6	216	307.5	480 channels
	023	MGL1408MCS04B	50	8000	2	18	ALL	9	6600	9	216	307.5	636 channels
	024	MGL1408MCS062	50	8000	2	18	2 & 3	6	3300	6	216	307.5	636 channels
	025	MGL1408MCS063	50	8000	2	18	2 & 3	6	3300	6	216	307.5	636 channels
	026	MGL1408MCS063A	25	6000	1	9	2 & 3	6	3300	6	216	307.5	480 channels
	027	MGL1408MCS064	25	6000	1	9	2 & 3	6	3300	6	216	307.5	480 channels
	028	MGL1408MCS04A	62.5	8000	2	18	All	9	6600	9	216	307.5	636 channels
	029	MGL1408MCSA4A	75	8000	2	18	All	9	6600	9	216	307.5	636 channels
	030	MGL1408MCS071	50	8000	2	18	2 & 3	6	3300	6	216	307.5	636 channels